



TSM100T Tone Speaker Module (AlphaLinQ™ 100 Series)



ARCHITECTS' AND ENGINEERS' SPECIFICATIONS

The nurse-call Tone Speaker Module(s) shall be Alpha Communications® **TSM100T** AlphaLinQ™ or approved equal. Tone Speaker Module(s) shall snap into the corresponding **MT** series modular panel frame(s).

TSM100T Tone Speaker Module(s) shall be finished in Titanium and shall feature a momentary Tone-Off pushbutton and Tone-Off LED.

Contractor shall observe all local and national electrical and building codes.

TSM100T TONE SPEAKER MODULE (ALPHALINQ™ 100 SERIES)



The **TSM100T** Tone Speaker Modules are designed to be used with Alpha Communications® AlphaLinQ™ 100 series nurse-call system Master Stations.

The **TSM100T** mounts into the '**MT**' series modular frame and provides the tone signaling when a call is placed on the AlphaLinQ™ 100 series nurse-call system. A Tone-Off Button and Tone-Off LED are also provided on the **TSM100T**.

All **TSM100T** tone speaker modules are 3.94"w x 3.94"h (100mm x 100mm), and are made to snap into the **MT** series modular panel trim frame(s). The **TSM100T** modules are used in conjunction with the **ELM116** (16-LED) modules and the associated housing(s) to provide a complete visual nurse-call master station.

To service the **TSM100T** modules, once installed, use the model **13510** key / tool unit

Alpha Communications

42 Central Drive • Farmingdale • NY • 11735-1202 • Phone: (631) 777-5500 • Fax: (631) 777-5599
TOLL-FREE: (800) 666-4800 • Web: www.alphacommunications.com • Email: info@alphacommunications.com

Copyright© 1998-2020 Alpha Communications® - All Rights Reserved.

Due to continuous product improvement, all colors, sizes, materials, finishes and specifications are subject to change without notice.