


Product Specification Sheet APS1096



Rev. 05/2018

E-114-3 Emergency Pull Cord Stations



E-114-3 EMERGENCY PULL CORD STATIONS

The Alpha Communications (R) / Cornell E-114-3 Emergency Pull station is used to initiate a system 'Emergency' signal. It may be used independently or connected with other call stations and/or intercom stations. The E-114-3 has a DPST Normally-Open switch that activates in a 'Latching' fashion, when the pull cord is pulled. In addition, a built-in RED 'Call-Placed' lamp will light when the pull cord station is activated.

Placing a call is accomplished by pulling on the pull cord. This type of 'Latching' pull cord station is typically canceled by sliding the switch back to the up (OFF) position. The E-114-3 station features a rugged stainless steel faceplate, with the word 'EMERGENCY' and "PULL FOR HELP" permanently silk-screened onto the faceplate.

FEATURES

- Simple, reliable operation
- Call cancel only at point of origin
- Red 'Call-Placed' Lamp
- Call registers at Master Station and on (optional) Dome Lamp
- Mounted on stainless steel faceplate permanently stamped with the word 'EMERGENCY' and 'PULL FOR HELP'

SPECIFICATIONS

Dimensions:	Height: 4.50" (114mm) Width: 2.75" (69mm) Depth: 1.50" (38mm) Projects: 0.50" (13mm) from mounting surface
Mounting:	Steel City #52171 box with Steel City #52C14 plaster ring, or Alpha Communications® Model #IH358 box with IH357 ring, or EXACT EQUAL. Vertical mount
Construction:	Reliable Components mounted to a Stainless Steel faceplate
Connection:	Plug-in Connectors

Alpha Communications

42 Central Drive • Farmingdale • NY • 11735-1202 • Phone: (631) 777-5500 • Fax: (631) 777-5599 TOLL-FREE: (800) 666-4800 • Web: www.alphacommunications.com • Email: info@alphacommunications.com

Copyright \odot 1998-2023 Alpha Communications $^{\odot}$ - All Rights Reserved.

Due to continuous product improvement, all colors, sizes, materials, finishes and specifications are subject to change without notice.